


—M22 x 1.5 FULL THREAD DEPTH  
Nutztiefe min 14



ALL OIL PORTS CLOSED PROPERLY AGAINST DUST FOR TRANSPORT AND STORAGE, E.G. WITH PLASTIC CLOSURE CAPS.

AE	--	20170418	TAU2ATB	tau2atb	lbs2po	BRZ DC-MA/EPC2-BR	ECR69259
AA	--	20101224	Jr/Hc			7930 DC-MA/EPE1	erstellt
In.Change/Aend.		YYYYMMDD	Dwn/Ges.	Unfied. Gbr.	Releas./Freig.	BWN Resp. dept./Verantw. Abt.	Add. info./Zus. Info.
Lang./Spr. EN/DE	Syst. PE	Wght./Gew.	<b>Rexroth Bosch Group</b>		HY GEAR PUMP HY-ZAHNRADPUMPE		Sheet/Bt 1/1
	.	Scale/M.stab 1:1	OFFER DRAWING ANGEBOTSZEICHN.		Doc.type AGZ	RA51474920	DP/TD 001
MNR			Repl. for AD-51MAEPQ892			Repl. by	Ind. AE
							Forma A2