

OPERATING CONDITIONS ACCORDING TO Y 510 201 598



CW ROTATION SHOWN.
CCW ROTATION PUMPS HAVE PRESSURE AND SUCTION PORT ON OPPOSITE SIDE.
PUMP MUST BE DRIVEN IN PROPER DIRECTION ONLY

***: WITH SUCTION PRESSURE ≥ 0.9 BAR (ABS.) AT SUCTION PORT

ALL OIL-PORTS CAPPED DUSTPROOF DURING TRANSPORT AND STORING,
E.G. WITH PLASTIC PLUGS

***: FOR USAGE IN POWER STEERING APPLICATIONS IN CASE OF MALFUNCTION OF THE STEERING PUMP THE VEHICLE MANUFACTURER HAS TO ASSURE A FAIL-SAFE OPERATION OF THE STEERING SYSTEM ACCORDING ECE R-79.

general tolerances for/Allgemeintoleranzen fuer		
lin.dim./L.masse	radii/Radien	angles/Winkel
± 0.3	-	$\pm 1^\circ$
all linear dimensions in/ Alle Laengenn Masse in		mm
drawing standard/ Zeichnungsstandard	ISO Standard	
hist. document no./ Hist. Dokumentnr.	43024 1288	

AT	--		20220420	CPV2KOR	LAG5SI	Ien2si	7930 DC-MO/EGE1	ECR 104289				
AA	--		20060321	kae9nue			7930 DC-MA/EPE	Erstellt				
Ind./Change/Aend.			YYYYMMDD	Drawn/Ges.	Gefertigt/Berf.	Released/Freigib.	BWN Resp. depl./Verantw.f. Abt.	Add. info./Zus. Info.				
Lang./Spr. EN/DE	Syst. PE	Wght./Gew. . / .	 A Bosch Company				HYDRAULIC GEAR PUMP AZPF HYDROAZAHNRADPUMPE		Sheet/Bl. 1/1			
	.	Scale/M.:stab 1:2	OFFER DRAWING ANGEBOTSZEICHN.				Doc. type AGZ RA51217862	DP/TD 001	Ind. A1	Format A2		
MNR					Repl. for			Repl. by				