


# Proportional pressure relief valve

RA 29166/08.04

1/10

## Model DBETR

Nominal size 6  
Component series 1X  
Maximum operating pressure 350 bar (5076 PSI)  
Maximum flow 3 L/min (0.79)



## Table of contents

### Contents

Features	
Ordering details	
Standard types	
Symbol	
Function, section	
Technical data	
Electrical connections, plug-in connectors	
Characteristic curves	
Unit dimensions	

## Features

Page	
1	– Valve for electrical remote control of pressure
2	– Direct operated proportional pressure relief valve, of poppet design
2	– Proportional solenoid actuation with inductive position transducer (pressure balanced)
3	– For subplate mounting:
3	Porting pattern to ISO 4401-03-02-0-94
4, 5	Subplates to catalogue sheet RE 45052 (separate order), see page 9
6	– Electrical closed loop position control of the spring pre-tension, hence low hysteresis
7, 8	– Good repeatability
9	– Valve and electronic control from one source
	– Control electronics:
	• Analog amplifier VT-VRPA1-100-1X/ in Euro card format (separate order), see page 5
	• Digital amplifier VT-VRPD-1-1X/V0/0 in Eurocard format (separate order), see page 5
	• Analogue amplifier of modular design VT-MRPA1-100-1X/V0/0 (separate order), see page 5


Ordering details

DBETR-1X/		G24	K4		*
Component series 10 to 19 (10 to 19: unchanged installation and connection dimensions)		= 1X			
<b>Pressure stage:</b> Up to 30 bar (435 PSI)		= 30			Further details in clear text  <b>M =</b> NBR seals, suitable for mineral oil (HL, HLP) to DIN 51524  <b>V =</b> FKM seals  <b>Electrical connections</b>  <b>K4 =</b> Without plug-in connector with component plug to DIN EN 175301-803 for the proportional solenoid and GSA20 for the position transducer Plug-in connector – separate order, see page 6
Up to 80 bar (1160 PSI)		= 80			
Up to 180 bar (2611 PSI)		= 180			
Up to 230 bar (3336 PSI)		= 230			
Up to 315 bar (4569 PSI)		= 315			
Up to 350 bar (5076 PSI)		= 350			
<b>Control electronics supply voltage</b> 24 V DC		= G24			

Standard types

Type	Material number
DBETR-1X/30G24K4M	R900954438
DBETR-1X/80G24K4M	R900334966
DBETR-1X/180G24K4M	R900491698
DBETR-1X/230G24K4M	R900370146
DBETR-1X/315G24K4M	R900485944
DBETR-1X/350G24K4M	R900352424

## Symbol



## Function, section

Proportional pressure relief valve type DBETR is a remote control valve. In design terms it is a direct operated pressure relief valve of poppet design.

This valve regulates pressure in proportion to the electrical command value.

The valve consists basically of a housing (1), proportional solenoid (2) with inductive positional transducer (3), valve seat (4) and valve poppet (5).

Pressure is set by adjusting the command value potentiometer (0 to 9 V). Adjusting the command value causes tensioning of the compression spring (2) via the electronic controls and the proportional solenoid (6). Tensioning of the compression spring (6), i.e. the position of the spring plate (7), is sensed by the inductive positional transducer (3). Any deviations from the command value are corrected by the closed loop positional control.

The use of this principle eliminates the effect of solenoid friction.


Advantages: – Low hysteresis  
– Good repeatability

If the command value is zero or in the event of a power failure to the proportional solenoid or cable breakage at the positional transducer the lowest possible setting pressure will be set.

### Note!

To ensure optimum valve function bleeding must be carried out at the commissioning stage:

- Remove item 8,
- Pour pressure fluid into open screw hole at item 8,
- When no further bubbles appear screw in item 8.
- Emptying of tank lines is to be avoided. With the appropriate installation conditions, a back pressure valve is to be installed (back pressure approx. 2 bar).



**Technical data** (for applications outside these parameters, please consult us!)

General				
Weight		kg (lbs)	4.0 (8.8)	
Installation		Preferrably horizontal		
Storage temperature range		°C (F)	– 20 ... +80 (– 4 ... + 176)	
Ambient temperature range		°C (F)	– 20 ... +50 (– 4 ... + 122)	
Hydraulic [measured with HLP 46 at 40°C ± 5°C (104°F ± 41°F )]				
Operating pressure	– Port P	bar (PSI)	... 350 (5076)	
	– Port T, with pressure control	bar (PSI)	... 2 (29)	
	– Without pressure control, T port	bar (PSI)	... 100 (1450)	
Max. settable pressure	– Pressure stage 30	bar (PSI)	30 (435)	
	– Pressure stage 80	bar (PSI)	80 (1160)	
	– Pressure stage 180	bar (PSI)	180 (2611)	
	– Pressure stage 230	bar (PSI)	230 (3336)	
	– Pressure stage 315	bar (PSI)	315 (4569)	
	– Pressure stage 350	bar (PSI)	350 (5076)	
Min. settable pressure			(See $p_{\min}$ - $q_v$ -characteristic curves on pages 7 and 8)	
Max. flow	– Pressure stage 30	L/min (GPM)	3 (0.79)	
	– Pressure stage 80	L/min (GPM)	3 (0.79)	
	– Pressure stage 180	L/min (GPM)	3 (0.79)	
	– Pressure stage 230	L/min (GPM)	3 (0.79)	
	– Pressure stage 315	L/min (GPM)	2 (0.53)	
	– Pressure stage 350	L/min (GPM)	2 (0.53)	
Pressure fluid			Mineral oil (HL, HLP) to DIN 51524, Other pressure fluids on request!	
Pressure fluid temperature range		°C (F)	– 20 ... + 80 (– 4 ... + 176)	
Max. permissible degree of pressure fluid contamination Cleanliness class to ISO 4406 (c)			Class 20/18/15 <sup>1)</sup>	
Viscosity range		mm <sup>2</sup> /s (SUS)	15 ... 380 (69.5 ... 1761)	
Hysteresis		%	< 1 of max. settable pressure	
Repeatability		%	< 0.5 of max. settable pressure	
Linearity		%	< 1.5 of max. settable pressure	
Typical variation		%	± 3 of max. settable pressure	
Stepped response $T_u + T_g$ (0 to 100 %), dependent on the system			$p_{\min} - p_{\max}$	$p_{\max} - p_{\min}$
– Pressure stage 30, 80, 180		ms	100	50
– Pressure stage 230, 315,		ms	150	100

<sup>1)</sup> The cleanliness class stated for the components must be adhered too in hydraulic systems. Effective filtration prevents faults from occurring and at the same time increases the component service life.

For the selection of filters see catalogue sheets RE 50070, RE 50076, RE 50081, RE 50086 and RE 50058.

**Technical data** (for applications outside these parameters, please consult us!)**Electrical** (solenoid)

Supply voltage	V	24 DC
Max. power consumption	VA	50
Coil resistance	Ω	10
– Cold value at 20 °C		
– Max. warm value	Ω	13.9
Duty	%	100
Electrical connections	With component plug to DIN EN 175301-803	
	Plug-in connector to DIN EN 175301-803 <sup>1)</sup>	
Schutzart nach EN 60529	IP65 with mounted and fixed plug-in connector	

**Electrical** (inductive position transducer)

Coil resistance	– Total resistance of the coils at 20 °C (68 °F)	1 and 2	2 and $\frac{1}{2}$	$\frac{1}{2}$ and 1
(see also page 6)	Ω	31.5	45.5	31.5
Electrical connections		With component plug GSA20		
		Plug-in connector GM 209N (Pg9) with flat seal <sup>1)</sup>		
Inductivity	mH	6 ... 8		
Oscillator frequency	kHz	2.5		
Protection to EN 60529		IP65 with mounted and fixed plug-in connector		

<sup>1)</sup> Separate order, see page 6

**When connecting the electrics, the protective conductor (PE  $\frac{1}{2}$ ) must be connected according to the relevant regulations.**

**Control electronics** (separate order)


Amplifier in Eurocard format	Analogue	VT-VRPA1-100-1X/ to catalogue sheet RE 30118
	Digital	VT-VRPD-1-1X/V0/0 to catalogue sheet RE 30125
Amplifier of modular design	VT-MRPA1-100-1X/V0/0 to catalogue sheet RE 30221	

**Note:** For details regarding the environmental simulation test covering EMC (electro-magnetic compatibility), climate and mechanical loading see RE 29166-U (declaration regarding environmental compatibility).


## Electrical connections, plug-in connectors - nominal dimensions in mm (inches)

### Proportional solenoid

Connection at component plug




Connection at plug-in connector




To amplifier

Plug-in connector to DIN EN 175301-803

Separate order under Material No. **R901017011** (plastic version)


### Inductive position transducer









Plug-in connector GM 209N (Pg9) with flat seal GM 207-3







Separate order under Material No. **R900013674** (plastic version)

Flat seal GM 207-3

Separate order under Material No. **R900013675**


**Characteristic curves** - measured with HLP-46,  $\vartheta_{oil} = 40^{\circ}\text{C} \pm 5^{\circ}\text{C}$  ( $104^{\circ}\text{F} \pm 41^{\circ}\text{F}$ ) and **without back**




**Characteristic curves** - measured with HLP-46,  $\vartheta_{oil} = 40^{\circ}\text{C} \pm 5^{\circ}\text{C}$  (104°F  $\pm$  41°F) and **without** back pressure




## Unit dimensions - nominal dimensions in mm (inches)



- 1 Valve housing
- 2 Proportional solenoid with inductive position transducer
- 3 Name plate
- 4 Blind hole
- 5.1 Plug-in connector to DIN EN 175301-803, separate order, see page 6
- 5.2 Plug-in connector to GM209 (Pg9) manufacturer Hirschmann; separate order, see page 6
- 6 Space required to remove the plug-in connector
- 7 Identical seal rings for P, T and blind hole
- 8 Machined valve mounting surface, location of the ports to ISO 4401-03-02-0-94  
Deviations from the standard:
  - Locating pin not present
  - „A“ and „B“ ports **not** drilled
- 9 Bleed screw
- 10 Lock nut 27A/F
- 11 Internal hexagon 8A/F



Subplates to catalog sheet RE 45052 and valve fixing screws must be ordered separately.

**Subplates:** G 341/01, G 1/4 (SAE-4; 7/16-20)  
G 342/01, G 3/8 (SAE-6; 9/16-18)

### Valve fixing screws:

(not included within the scope of supply)

Due to strength (tensile) reasons only use the following valve fixing screws:

**4 S.H.C.S. ISO 4762 - M5 x 50 - 10.9-flZn-240h-L**

(friction value 0.08 - 0.14 to VDA 235-102);

Tightening torque  $M_A = 7 \text{ Nm} \pm 10\%$

Separate order, Material No. **R913000064**.

Notes

---

Bosch Rexroth Corp.  
Industrial Hydraulics  
2315 City Line Road  
Bethlehem, PA 18017-2131  
USA  
Telephone (610) 684-8300  
Facsimile (610) 694-8467  
[www.boschrexroth-us.com](http://www.boschrexroth-us.com)

© This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth Corporation. Without their consent it may not be reproduced or given to third parties.

The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging.

## Notes

---

Bosch Rexroth Corp.  
Industrial Hydraulics  
2315 City Line Road  
Bethlehem, PA 18017-2131  
USA  
Telephone (610) 684-8300  
Facsimile (610) 694-8467  
[www.boschrexroth-us.com](http://www.boschrexroth-us.com)

© This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth Corporation. Without their consent it may not be reproduced or given to third parties.

The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging.

## Notes

---

Bosch Rexroth Corp.  
Industrial Hydraulics  
2315 City Line Road  
Bethlehem, PA 18017-2131  
USA  
Telephone (610) 684-8300  
Facsimile (610) 694-8467  
[www.boschrexroth-us.com](http://www.boschrexroth-us.com)

© This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth Corporation. Without their consent it may not be reproduced or given to third parties.

The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging.