

Pressure relief valve, direct operated Type DBD



K4942-1

Features

- ▶ Screw-in cartridge valve
- ▶ 8 pressure ratings
- ▶ 2 adjustment types, optionally:
 - Grub screw with internal hexagon
 - Hand wheel

- ▶ Size 4
- ▶ Component series 1X
- ▶ Maximum operating pressure 500 bar
- ▶ Maximum flow 20 l/min



Contents

Ordering code	2
Function, section, symbol	3
Technical data	4
Characteristic curves	5
General information	5
Dimensions	6
Mounting cavity	7

Type-examination tested safety valves type DBD...K according to Pressure Equipment Directive 2014/68/EU (in the following shortly PED)

Ordering code	8
Deviating technical data	8
Safety instructions	9
Characteristic curves	9
Related documentation	11

Ordering code

01	02	03	04	05	06	07	08	09
DBD		4	K	1X	/		V	*

01	Pressure relief valve, direct operated	DBD
----	--	------------

Adjustment type for pressure adjustment

02	Grub screw with internal hexagon	S
	Hand wheel	H

03	Size 4	4
----	--------	----------

Type of connection

04	As screw-in cartridge valve (cartridge)	K
----	---	----------

05	Component series 10 ... 19 (10 ... 19: unchanged installation and connection dimensions)	1X
----	--	-----------

Pressure rating

06	Set pressure up to 25 bar	25
	Set pressure up to 50 bar	50
	Set pressure up to 100 bar	100
	Set pressure up to 200 bar	200
	Set pressure up to 315 bar	315
	Set pressure up to 350 bar	350
	Set pressure up to 420 bar	420
	Set pressure up to 500 bar	500

Seal material (observe compatibility of seals with hydraulic fluid used, see page 4)

07	FKM seals	V
----	-----------	----------

Equipment Directive

08	Without type-examination procedure	no code
	Type-examination tested safety valve according to PED 2014/68/EU (see ordering code on page 8)	E

09	Further details in the plain text	
----	-----------------------------------	--

Notice

Preferred types and standard units are contained in the EPS (standard price list).


Function, section, symbol

Pressure valves of type DBD are direct operated pressure relief valves to be installed in block designs. They are used for limiting a system pressure.

The system pressure can be set via the adjustment type (5).

In the initial position the valve is closed. Via control line (1) and poppet (2), the pressure in the main port ① acts on the spring plate (3). If the pressure in the main port ① rises above the value set at the compression spring (4), the poppet (2) opens and the hydraulic fluid flows into the main port ②.

▼ Cross-section DBD



- 1 Control line
- 2 Poppet
- 3 Spring plate
- 4 Compression spring
- 5 Adjustment type

Technical data

General			
Weight		kg	approx. 0.3
Installation position			Any
Ambient temperature range		°C	−20 ... +80
Hydraulic			
Maximum operating pressure	– Input	bar	500
	– Output	bar	315 (50 bar at set pressure 500 bar)
Maximum set pressure		bar	25; 50; 100; 200; 315; 350; 420; 500
Maximum flow		l/min	20
Hydraulic fluid			see table below
Hydraulic fluid temperature range		°C	−20 ... +80
Viscosity range		mm²/s	10 ... 800
Maximum admissible degree of contamination of the hydraulic fluid, cleanliness class according to ISO 4406 (c)			Level 20/18/15 1)

Hydraulic fluid

Hydraulic fluid		Classification	Suitable sealing materials	Standards	Data sheet
Mineral oils		HL, HLP	FKM	DIN 51524	90220
Environmentally acceptable	Insoluble in water	HEES	FKM	ISO 15380	90221
	Soluble in water	HEPG	FKM	ISO 15380	90221

Notice

- Further information and details on using other hydraulic fluids are available in the above data sheets or on request.
- Restrictions are possible with the technical valve data (temperature, pressure range, service life, maintenance intervals, etc.)!
- The flash point of the hydraulic fluid used must be 40 K above the maximum solenoid surface temperature.
- **Environmentally acceptable:** If environmentally acceptable hydraulic fluids are used that are also zinc-soluble, there may be an accumulation of zinc.


Notice

For applications outside these values, please consult us!


¹⁾ Cleanliness levels specified for the components must be maintained in the hydraulic systems. Effective filtration prevents malfunctions and simultaneously extends the service life of the components.

Characteristic curves

▼ p_E - q_V characteristic curve



▼ Δp - q_V characteristic curve



Notice

- ▶ Characteristic curves measured with HLP46, $\vartheta_{oil} = 40 \pm 5 \text{ }^\circ\text{C}$.
- ▶ The characteristic curves apply to output pressure = zero in the entire flow range and were measured without housing resistance.

General information

Hydraulic counter pressures in the main port ② (T) add 1:1 to the response pressure of the valve set at the adjustment.


Example:

- ▶ Pressure adjustment of the valve due to spring preload (item 4 on page 3) $p_{spring} = 200 \text{ bar}$
- ▶ Hydraulic counter pressure in the main port ② (T):
 $p_{hydraulic} = 50 \text{ bar}$

→ Response pressure = $p_{spring} + p_{hydraulic} = 250 \text{ bar}$


Dimensions

▼ DBD



- 1.1** Adjustment type "S", internal hexagon SW5
- 1.2** Adjustment type "H", hand wheel
- 2** Lock nut SW17, tightening torque $M_A = 10+5$ Nm
- 3** Sechskant SW17, tightening torque when screwing in $M_A = 23\pm 2$ Nm
- 4** Embossed type designation

- ① = Main port 1 (P)
- ② = Main port 2 (T)

Mounting cavity▼ **R/DBD . 4K; 2 main ports; thread M14×1**

1) Depth for moving parts

2) All seal ring insertion faces are rounded and free of burrs

3) With countersink

4) Visual inspection

① = Main port 1 (P)

② = Main port 2 (T), can optionally be arranged at the circumference

Tolerance for all angles ±0.5°

Type-examination tested safety valves

The functionality of these valves corresponds to that of the standard series (see page 3). Valves of type DBD..1X/..E are, however, type-examination tested pressure relief valves according to the Pressure Equipment Directive 2014/68/EU and intended for use as safety valves.

At the factory, the response pressure is set to a fixed maximum value using the adjustment type. Afterwards, the safety valve is sealed.

The safety valves are available with graded response pressures (in 5 bar steps). With valve versions equipped with rotary knob or hand wheel, the valve spring can be unloaded by the user and a response pressure lower than the factory setting can be set without the need for removing the lead seal.

Ordering code: Type-examination tested safety valves type DBD ¹⁾

Designation	Component marking	Maximum flow $q_{V \max}$ [l/min]	Pre-set response overpressure p [bar]
DBDS 4 K1X/ <input type="checkbox"/> E	TÜV.SV.- <input type="checkbox"/> -1038.4.F.G.p	10	60 ... 315
DBDH 4 K1X/ <input type="checkbox"/> E		17	320 ... 500

☐ Pressure in the type designation is to be entered by the customer, pressure adjustment ≥ 60 bar and possible in 5-bar steps.

☐ Value entered at the factory.

Deviating technical data: Type-examination tested safety valves type DBD ¹⁾

General		
Ambient temperature range	°C	–10 ... +60
Conformity	CE according to Pressure Equipment Directive 2014/68/EU	
Hydraulic		
Set response pressure	bar	See last figure of the component marking above
Maximum counter pressure in the discharge line	bar	See characteristic curves on page 9 and 10
Maximum flow	l/min	The last but one figure of the component marking attached at the safety valve is always binding, see above. For valve types which have a variable maximum flow depending on the response pressure, the discharge coefficient is specified at this place (see also page 10)
Hydraulic fluid	Hydraulic fluids according to DIN 51524: Hydraulic oils HL and HLP are suitable for safety valves with FKM seals.	
Hydraulic fluid temperature range (= TS)	°C	–10 ... +60
Viscosity range	mm²/s	12 ... 230

Notice

For applications outside these values, please consult us!

¹⁾ Component series 1X, according to Pressure Equipment Directive 2014/68/EU

Safety instructions: Type-examination tested safety valves type DBD 1)

- ▶ Before ordering a type-examination tested safety valve, it must be observed that for the desired **response pressure p** , the maximum admissible **flow q_{Vmax}** of the safety valve must be larger than the maximum possible flow of the system/accumulator to be secured. According to the Pressure Equipment Directive **2014/68/EU**, the increase in the system pressure due to the flow must not exceed 10% of the set response pressure (see component marking page 8).
- ▶ The maximum admissible flow **q_{Vmax}** stated in the component marking must not be exceeded.
- ▶ Discharge lines of safety valves must end in a risk-free manner. An accumulation of fluids in the discharge system must not be possible (see data sheet AD2000 A2).

Application notes must always be observed!

- ▶ In the plant, the response pressure specified in the component marking is set with a flow of 1 l/min.
- ▶ The maximum flow stated in the component marking applies for applications without counter pressure in the discharge line (port **T**).
- ▶ By removing the lead seal at the safety valve, the approval according to the Pressure Equipment Directive becomes void!
- ▶ Basically, the requirements of the Pressure Equipment Directive and of data sheet AD 2000 A 2 have to be observed.
- ▶ It is recommended to secure type-examination tested safety valves against inadmissible disassembly by means of wiring and sealing with the housing/block (bore available in the adjustment type).

Notice

The system pressure increases by the counter pressure in the discharge line (port **T**) due to the increasing flow. (Observe the data sheet AD 2000 A 2, point 6.3)
 To ensure that this increase in system pressure caused by the flow does not exceed the value of 10% of the set response pressure, the admissible flow has to be reduced dependent on the counter pressure in the discharge line (port **T**) (see diagrams on page 9 and 10).

Characteristic curves: Counter pressure in the discharge line

In principle, the valve should be operated without counter pressure in the discharge line, if possible. In case of counter pressure in the discharge line, the maximum possible flow is reduced. There is a relationship between maximum counter pressure **p_T** in the discharge line and flow **q_V** , which can be seen from the following characteristic curve. Characteristic curves for intermediate values of the response pressure which are not listed must be determined by means of interpolation.

When the flow approaches zero, the maximum counter pressure **p_T** is in each case 10% of the response pressure. With increasing flow, the maximum counter pressure **p_T** decreases.


Interpolation of intermediate values from the diagram

1. At the axis **p_T** , mark 1/10 of the value of **p_A** .
2. Determine the next lower and the next higher characteristic curve for this point. The point marked at **p_T** divides the section between lower and higher characteristic curve on the **p_T** axis with a certain percentage.
3. At the **q_{Vmax}** axis, divide the section between next lower and next higher characteristic curve in the same percentage as the section at the **p_T** axis. From the zero position flow on the **q_{Vmax}** axis determined in that way, draw a straight line to the value on the **p_T** axis marked before.
4. Mark the system flow to be secured at the **q_{Vmax}** axis.
5. Read off the maximum counter pressure for this value using the line at the **p_T** axis drawn before.

1) Component series 1X, according to the Pressure Equipment Directive 2014/68/EU

Characteristic curves: Counter pressure in the discharge line

Diagram for determining the maximum counter pressure p_T in the discharge line at port **T** of the valve dependent on the flow q_{Vmax} for valves DBD.4...1X/...E with different response pressures p_A .



Characteristic curves	Response pressure p_A [bar]
1	60
2	100
3	200
4	315
5	320
6	350
7	500

Characteristic curves for intermediate values can be generated by interpolation. Further explanations can be found on page 9.

- p_A Response pressure in bar
- p_T Maximum counter pressure in the discharge line (port **T**) in bar
- q_{Vmax} Maximum flow in l/min

Determination of the maximum counter pressure

Example (with already existing characteristic curve):
Flow of the system / accumulator to be secured:
 $q_{Vmax} = 5 \text{ l/min}$
Safety valve set to: $p_A = 500 \text{ bar}$.
Read off the maximum counter pressure p_T of approx. 36 bar from the diagram (see arrows, characteristic curve 7).

Related documentation

- ▶ Safety equipment against excessive pressure – safety valves
- ▶ Hydraulic fluids on mineral oil basis
- ▶ Environmentally compatible hydraulic fluids
- ▶ Flame-resistant, water-free hydraulic fluids
- ▶ Flame-resistant hydraulic fluids – containing water (HFAE, HFAS, HFB, HFC)
- ▶ Reliability characteristics according to EN ISO 13849
- ▶ Hydraulic valves for industrial applications

Data sheet AD 2000 A 2

Data sheet 90220

Data sheet 90221

Data sheet 90222

Data sheet 90223

Data sheet 08012, 90294

Operating instructions 07600-B

Bosch Rexroth AG

Zum Eisengießer 1
97816 Lohr am Main
Germany
Tel. +49 9352 18-0
info.ma@boschrexroth.de
www.boschrexroth.com

© Bosch Rexroth AG 2022. All rights reserved, also regarding any disposal, exploitation, reproduction, editing, distribution, as well as in the event of applications for industrial property rights. The data specified within only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging.